


# **GARRETT** **SmartScan**

Integrated System for Garrett *PD 6500i*™ and *MZ 6100*™



**SECURITY THERMAL SCREENING SYSTEM**



**GARRETT**  
**SmartScan™**  
THERMAL SCREENING SYSTEM

Effortless temperature screening. Garrett *SmartScan*™ technology allows body temperature measurements to be taken during your normal security screening with no extra hassle or anxiety. Seamless integration of *SmartScan* into Garrett walk-through metal detectors allows your security checkpoint to become an efficient, multi-functional no-contact station.



## KEY FEATURES:

- Cost effective, fast temperature detection of incoming traffic
- Does not slow down existing screening process
- No technical staff needed to make initial temperature evaluations, reducing staffing costs and the potential for human error
- Battery-operated for ease of use and optimal flexibility
- Intuitive status indicators for startup, calibration, misreads, and elevated temperature alarms
- A constant temperature reference is not required for operation
- Visual and audible alarm options
- No dangerous cords or cables or unstable tripod required. No additional components that require floor space.
- Quick start operation (single button to power on and begin using)
- Avoids false alarming by intelligently blocking non-facial high temperature sources that would mistakenly trigger an alarm

**Contactless, cost effective metal detection and temperature scanning offers peace of mind for your patrons.**

## SMARTSCAN IS THE SMART CHOICE.

No extra screening step is required to take temperatures. The *SmartScan* system will scan temperatures, discretely provide a “Go” or “No Go” indication to the operator, and allow guests to proceed through the detector with no delays.

Temperature detection and metal detection functions may be used independently or together for simultaneous operation.


This solution is offered as an add-on accessory for new Garrett *PD 6500i* or *MZ 6100* walk-through metal detectors or it can be easily retrofitted into already-installed Garrett *PD* or *MZ* detectors. Garrett’s *Quick-Q™* cellphone elimination technology can be used in conjunction with *SmartScan* to further expedite the screening process and promote touchless screening.



**Simultaneous health and safety screening with no long lines!**

# GARRETT SmartScan

Upgrade your Garrett PD 6500i  
or MZ 6100 walk-through metal  
detector with the SmartScan  
thermal screening system.



## RECOMMENDED ACCESSORY

### Garrett IR Digital Thermometer

Non-Contact Infrared Forehead Thermometer  
PN: 1613200



### Fully HIPAA compliant, FDA 510(k) clearance pending

Note: measurements taken from SmartScan should not be solely or primarily relied upon to diagnose or rule out a diagnosis for any disease. An elevated body temperature indication from SmartScan should be secondarily confirmed by qualified personnel according to your health screening practices and procedures using medical-grade equipment.

SmartScan, Thermal Screening, 30" PN: 1178000

SmartScan, Thermal Screening, 32.5"\* PN: 1178020

\* 32.5" ADA-compliant passageway

garrett.com



MADE IN THE USA

Email: [smartsan@garrett.com](mailto:smartsan@garrett.com)

Tel: 1.972.494.6151

Toll Free (U.S. and Canada): 1.800.234.6151